



Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Phosphor Bronze Sleeves, Red

By Bryant
Catalog # FSPLCQM3R

Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Phosphor Bronze Sleeves, Red



Features

- Premium Quality and High Performance Design

General

Application	Interconnect
Color	Red
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	3) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103822

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3 TIA-604-FOCIS
----------------------	------------------------------

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A Hubbell brand