



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Black

By Bryant
Catalog # FSPLCQM6BK

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Black



Features

- Premium Quality and High Performance Design

General

| | |
|------------------------------|-----------------|
| Application | Interconnect |
| Color | Black |
| EU RoHS Indicator | No |
| Enclosure Type | Various |
| Environmental Conditions | Indoor |
| Item Type | 6) LC Quad |
| Material | Phosphor Bronze |
| Material - Mounting Hardware | Snap-In |
| Number Of Ports | 24 |
| Repeatability | 0.2 dB |
| Service Life | 500 matings |
| Single/Multimode | MM |
| Temperature Rating | -40C to +85C |
| UPC | 662620103891 |

Dimensions

| | |
|--------------|-------------|
| Display Size | 5.1" X 1.1" |
|--------------|-------------|

Electrical Ratings

| | |
|----------------|------------|
| Connectivity | Receptacle |
| Insertion Loss | 0.30 dB |
| Return Loss | 26 |

Conductor Related

| | |
|------------|------------|
| Fiber Size | 125 Micron |
| Fiber Type | Multimode |

Certifications And Compliance

| | |
|----------------------|------------------------------|
| Industry Standard(s) | TIA-568-C.3 TIA-604-FOCIS |
|----------------------|------------------------------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 4 |
|-----------------|---|

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-FSPLCQM6BK-SPEC-EN | REV 6/2024