



# Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Red

By Bryant  
Catalog # FSPLCQM6R

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Red



## Features

- Premium Quality and High Performance Design

## General

Adapter Type	LC Quad
Application	Interconnect
Catalog Number	FSPLCQM6R
Color	Red
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103914

## Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

## Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

## Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

## Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
	TIA-604-FOCIS

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-FSPLCQM6R-SPEC-EN | REV 6/2024