



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Beige

By Bryant
Catalog # [FSPLCQS6BE](#)



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Beige

Features

- Premium Quality and High Performance Design

Application

Interconnect

General

Adapter Type	LC Quad
Catalog Number	FSPLCQS6BE
Color	Beige
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620103921

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 55

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPLCQS6BE](#)