



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Orange

By Bryant
Catalog # [FSPLCQS6OR](#)

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Orange



Features

- Premium Quality and High Performance Design

Application

- Interconnect

General

Adapter Type	LC Quad
Catalog Number	FSPLCQS6OR
Color	Orange
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620211541

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 55

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPLCQS6OR](#)