



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Red

By Bryant
Catalog # [FSPLCQS6R](#)



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Red

Features

- Premium Quality and High Performance Design

Application

- Interconnect

General

| | |
|------------------------------|-----------------|
| Adapter Type | LC Quad |
| Catalog Number | FSPLCQS6R |
| Color | Red |
| EU RoHS Indicator | Yes |
| Enclosure Type | Various |
| Environmental Conditions | Indoor |
| Item Type | 6) LC Quad |
| Material | Phosphor Bronze |
| Material - Mounting Hardware | Snap-In |
| Number Of Ports | 24 |
| Repeatability | 0.2 dB |
| Service Life | 500 matings |
| Single/Multimode | SM/MM |
| Temperature Rating | -40C to +85C |
| UPC | 662620212159 |

Dimensions

| | |
|--------------|-------------|
| Display Size | 5.1" X 1.1" |
|--------------|-------------|

Electrical Ratings

| | |
|----------------|------------|
| Connectivity | Receptacle |
| Insertion Loss | 0.30 dB |
| Return Loss | 55 |

Conductor Related

| | |
|------------|------------|
| Fiber Size | 125 Micron |
| Fiber Type | Multimode |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• TIA-568-C.3• TIA-604-FOCIS |
|----------------------|---|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 4 |
|-----------------|---|

Product Assets

[Specifications - FSPLCQS6R](#)