



Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Yellow

By Bryant
Catalog # [FSPLCQS6Y](#)

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Yellow



Features

- Premium Quality and High Performance Design

Application

Interconnect

General

Color	<ul style="list-style-type: none">• Yellow• Yellow
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620211534

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FSPLCQS6Y-SPEC-EN | REV 7/2023