



Fiber Optic Panel Adapter, 72 Fiber, 6) 12-Fiber MTP, Phosphor Bronze Sleeves, Aqua

By Bryant
Catalog # FSPMTPAQ6

Fiber Optic Panel Adapter, 72 Fiber, 6) 12-Fiber MTP, Phosphor Bronze Sleeves, Aqua



Features

- Premium Quality and High Performance Design

General

Adapter Type	MPO
Application	Interconnect
Catalog Number	FSPMTPAQ6
Color	Aqua
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) MTP
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Temperature Rating	-40C to +85C
UPC	662620291918

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3 TIA-604-FOCIS
----------------------	------------------------------

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-FSPMTPAQ6-SPEC-EN | REV 6/2024