



# FSP Adapter Panel, MT-RJ, 12-Port, Loaded with 6) Multi Mode Duplex Adapters

By Bryant

Catalog # [FSPMTRJ6](#)



FSP Adapter Panel, MT-RJ, 12-Port, Loaded with 6) Multi Mode Duplex Adapters

## Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

## Application

Interconnect

## Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

## General

Adapter Type	MT-RJ
Catalog Number	FSPMTRJ6
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) MT-RJ
Material	Bronze, Phosphor
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none"><li>• Dimensions - 1.1" W X 5.1" H</li></ul>

- Finish - Durable black powder coat
- Material - 16ga cold rolled steel

Temperature Rating  
UPC

-40C to +85C  
662620817026

## Dimensions

Display Size 5.1" X 1.1"

## Electrical Ratings

Connectivity Receptacle  
Insertion Loss 0.75 dB Max  
Return Loss 26

## Conductor Related

Fiber Size 125 Micron  
Fiber Type Multimode

## Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

## Logistics

Carton Quantity 4

## Product Assets

[Specifications - FSPMTRJ6](#)