



FSP Adapter Panel, MT-RJ, 16-Port, Loaded with 8) Multi Mode Duplex Adapters

By Bryant
Catalog # [FSPMTRJ8](#)



FSP Adapter Panel, MT-RJ, 16-Port, Loaded with 8) Multi Mode Duplex Adapters

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	MT-RJ
Catalog Number	FSPMTRJ8
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	8) MT-RJ
Material	Bronze, Phosphor
Material - Mounting Hardware	Snap-In
Number Of Ports	8
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none"> • Dimensions - 1.1" W X 5.1" H

- Finish - Durable black powder coat
 - Material - 16ga cold rolled steel
- Temperature Rating
UPC
- 40C to +85C
662620817064

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
 Insertion Loss 0.75 dB Max
 Return Loss 26

Conductor Related

Fiber Size 125 Micron
 Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPMTRJ8](#)