




Fiber Optic Panel Adapter, 6-Fiber, 6) SC MTJR, Unloaded

By Bryant
Catalog # [FSPSC6X](#)

Fiber Optic Panel Adapter, 6-Fiber, 6) SC MTJR, Unloaded



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

General

Adapter Type	SC Simplex/LC Duplex
Application	Interconnect
Catalog Number	FSPSC6X
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) SC Simplex
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Performance	Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
	Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.1 dB
Service Life	500 matings
Temperature Rating	-40C to +85C
UPC	662620218380

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Return Loss	26

Conductor Related

Fiber Size	125 Micron
------------	------------

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
	TIA-604-FOCIS

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-FSPSC6X-SPEC-EN | REV 6/2024