



# Fiber Optic Panel Adapter, 8 Fiber, 8) SC MTJR, Unloaded

By Bryant  
Catalog # [FSPSC8X](#)

Fiber Optic Panel Adapter, 8 Fiber, 8) SC MTJR, Unloaded



## Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

## Application

Interconnect

## General

Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC Simplex/LC Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	8
Performance	<ul style="list-style-type: none"><li>• Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)</li><li>• Environmental - Operating temperature - 0 °C to +75 °C</li></ul>
Repeatability	0.1 dB
Service Life	500 matings
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620218397

## Dimensions

Display Size 5.1" X 1.1"

## Electrical Ratings

Connectivity Receptacle  
Insertion Loss 0.30 dB  
Return Loss 26

## Conductor Related

Fiber Size 125 Micron

## Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

## Logistics

Carton Quantity 4

## Product Assets

[Literature - FIBERHUBB N-Series Fiber Panels](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-FSPSC8X-SPEC-EN | REV 7/2023