



FSP Adapter Panel, SC/APC Simplex, 8- Port, Loaded with 8) Adapters

By Bryant
Catalog # FSPSCA8

FSP Adapter Panel, SC/APC Simplex, 8- Port, Loaded with 8) Adapters



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

General

Color	Green
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	8) SC Simplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	8
Performance	<ul style="list-style-type: none"> • Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical) • Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.1 dB
Service Life	500 matings
Single/Multimode	SM
Temperature Rating	-40C to +85C
UPC	662620829609

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • TIA-568-C.3 • TIA-604-FOCIS
----------------------	--

Logistics

Carton Quantity 4

Product Assets



A proud member of the Hubbell Family.