



FSP Adapter Panel, 6-Fiber, SC Duplex, 12-Port, Loaded with 6) Adapters, Zircon Sleeves, Blue

By Bryant
Catalog # FSPSCSS6



FSP Adapter Panel, 6-Fiber, SC Duplex, 12-Port, Loaded with 6) Adapters, Zircon Sleeves, Blue

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC Simplex
Catalog Number	FSPSCSS6
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	12) SC Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Specifications	<ul style="list-style-type: none">• Dimensions - 1.1" W X 5.1" H• Finish - Durable black powder coat

- Material - 16ga cold rolled steel
 - Sleeve Material - Zirconia Ceramic
- Temperature Rating
UPC
- 40C to +85C
662620212210

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 55

Conductor Related

Fiber Size 125 Micron
Fiber Type Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPSCSS6](#)