



FSP Adapter Panel, SC Duplex/ST-Style, 6-Port, Loaded with 3 Adapters, Phosphor Bronze

By Bryant
Catalog # FSPSCST3



FSP Adapter Panel, SC Duplex/ST-Style, 6-Port, Loaded with 3 Adapters, Phosphor Bronze

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC to ST Duplex
Catalog Number	FSPSCST3
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC to ST Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none"> • Dimensions - 1.1" W X 5.1" H

- Finish - Durable black powder coat
- Material - 16ga cold rolled steel
- Sleeve Material - Phosphor Bronze

Temperature Rating -40C to +85C
UPC 662620806976

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 26

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4