



FSP Adapter Panel, SC Duplex/ST-Style, 12-Port, Loaded with 6 Adapters, Phosphor Bronze

By Bryant
Catalog # FSPSCST6



FSP Adapter Panel, SC Duplex/ST-Style, 12-Port, Loaded with 6 Adapters, Phosphor Bronze

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC to ST Duplex
Catalog Number	FSPSCST6
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC to ST Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none"> • Dimensions - 1.1" W X 5.1" H • Finish - Durable black powder coat

- Material - 16ga cold rolled steel
 - Sleeve Material - Phosphor Bronze
- Temperature Rating
UPC
- 40C to +85C
662620816913

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
 Insertion Loss 0.30 dB
 Return Loss 26

Conductor Related

Fiber Size 125 Micron
 Fiber Type Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Specifications - FSPSCST6](#)