



Fiber Optic Panel Adapter, 12-Fiber, 6) SC-ST Duplex, Zircon Sleeves, Blue

By Bryant
Catalog # FSPSCSTD6

Fiber Optic Panel Adapter, 12-Fiber, 6) SC-ST Duplex, Zircon Sleeves, Blue

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC to ST Duplex
Catalog Number	FSPSCSTD6
Color	Blue
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC to ST Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Specifications	<ul style="list-style-type: none">• Dimensions - 1.1" W X 5.1" H• Finish - Durable black powder coat



	<ul style="list-style-type: none">• Material - 16ga cold rolled steel• Sleeve Material - Zirconia Ceramic
Temperature Rating	-40C to +85C
UPC	662620103723

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Specifications - FSPSCSTD6](#)



A Hubbell brand