



FSP Adapter Panel, 6-Fiber, ST Simplex, 6-Port, Loaded with 6 Adapters, Phosphor Bronze

By Bryant
Catalog # FSPST6

FSP Adapter Panel, 6-Fiber, ST Simplex, 6-Port, Loaded with 6 Adapters, Phosphor Bronze



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

General

Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Simplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Performance	<ul style="list-style-type: none">• Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)• Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620805023

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Insertion Loss 0.30 dB
Return Loss 26

Conductor Related

Fiber Size 125 Micron
Fiber Type Multimode

Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FSPST6-SPEC-EN | REV 7/2023