




FSP Adapter Panel, ST-Style, 6-Port, Unloaded

By Bryant
Catalog # [FSPST6X](#)

FSP Adapter Panel, ST-Style, 6-Port, Unloaded



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

General

Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Simplex
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Performance	<ul style="list-style-type: none">• Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)• Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.1 dB
Temperature Rating	-40C to +85C
UPC	662620806747

Dimensions

Display Size 5.1" X 1.1"

Electrical Ratings

Connectivity Receptacle
Return Loss 55

Conductor Related

Fiber Size 125 Micron

Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-FSPST6X-SPEC-EN | REV 7/2023