



# FSP Adapter Panel, 8-Fiber, ST Simplex, 8-Port, Loaded with 8 Adapter Phosphor Bronze

By Bryant  
Catalog # FSPST8



FSP Adapter Panel, 8-Fiber, ST Simplex, 8-Port, Loaded with 8 Adapter Phosphor Bronze

## Application

Interconnect

## Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

## General

Adapter Type	ST-Style Simplex
Catalog Number	FSPST8
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Simplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	8
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none"> <li>• Dimensions - 1.1" W X 5.1" H</li> <li>• Finish - Durable black powder coat</li> <li>• Material - 16ga cold rolled steel</li> </ul>

Temperature Rating	-40C to +85C
UPC	662620816777

## Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

## Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

## Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• TIA-568-C.3</li> <li>• TIA-604-FOCIS</li> </ul>
----------------------	--

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets

[Specifications - FSPST8](#)