



Fiber Adapter Panel, 6-Fiber, 3) ST Duplex, Phosphor Bronze, Blue

By Bryant
Catalog # FSPSTD3

Fiber Adapter Panel, 6-Fiber, Three ST Duplex, Phosphor Bronze



Application

Interconnect

Performance

- Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	ST-Style Duplex
Catalog Number	FSPSTD3
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Specifications	<ul style="list-style-type: none">• Dimensions - 1.1" W X 5.1" H• Finish - Durable black powder coat• Material - 16ga cold rolled steel

- Sleeve Material - Phosphor Bronze
- Temperature Rating
UPC
-40C to +85C
662620289243

Dimensions

Display Size
5.1" X 1.1"

Electrical Ratings

Connectivity
Insertion Loss
Return Loss
Receptacle
0.30 dB
26

Conductor Related

Fiber Size
Fiber Type
125 Micron
Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity
4

Product Assets

[Specifications - FSPSTD3](#)