



# Fiber Optic Panel Adapter, 12-Fiber, 6) ST Duplex, Zircon Sleeves, Blue

By Bryant  
Catalog # FSPSTDS6

Fiber Optic Panel Adapter, 12-Fiber, 6) ST Duplex, Zircon Sleeves, Blue



## Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

## General

Adapter Type	ST-Style Duplex
Application	Interconnect
Catalog Number	FSPSTDS6
Color	Blue
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	ST Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Performance	Electrical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
	Environmental - Operating temperature - 0 °C to +75 °C
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620214689

## Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

## Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

## Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

## Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
	TIA-604-FOCIS

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-FSPSTDS6-SPEC-EN | REV 6/2024