



Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Gray

By Bryant
Catalog # [GFBFHP20GY](#)

Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Gray

Features

- Blank face 1.5 horsepower motor control rated switch UL508 listed. Also listed to Underwriters Laboratories standard 943 for Class A GFCI
- If wired incorrectly there will be no power to the face or to downstream receptacles for added safety. (2) LED indicators provide immediate status of power, trip condition and ability to provide GFCI protection
- In addition to providing Class A GFCI protection, the HP series includes a 1.5 HP rating for motor control switching per UL508

General

Catalog Number	GFBFHP20GY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty



Style	Blank Face, 1.5HP
Type	Standard
UPC	883778450037

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Logistics

Carton Quantity	10
Pallet Quantity	2240

Product Assets

- [Catalog Page - WDK K-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - GFBFHP20GY](#)