



# Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Ivory

By Bryant  
Catalog # [GFBFHP20I](#)

Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Ivory



## Features

- Blank face 1.5 horsepower motor control rated switch UL508 listed. Also listed to Underwriters Laboratories standard 943 for Class A GFCI
- If wired incorrectly there will be no power to the face or to downstream receptacles for added safety. (2) LED indicators provide immediate status of power, trip condition and ability to provide GFCI protection
- In addition to providing Class A GFCI protection, the HP series includes a 1.5 HP rating for motor control switching per UL508

## General

Color	<ul style="list-style-type: none"><li>• Ivory</li><li>• Ivoire</li></ul>
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Blank Face, 1.5HP
Type	Standard
UPC	883778450044

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

## Related Products

- [GFBFST20I - Power Protection Devices, Self Test Faceless GFCI, 20A 125V, 2-Pole 3-Wire Grounding, Ivory](#)
- [GFBFHP20R - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Red](#)
- [GFBFHP20W - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, White](#)
- [GFBFHP20LA - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Light Almond](#)
- [GFBFHP20GY - Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Gray](#)



A proud member of the Hubbell Family.