



Power Protection Products, GFCI Linecords, Commercial, Auto Set, 15A 125V AC, 5-15R, 2' Cord Length, 4-6 mA Trip Level, Yellow

By Bryant
Catalog # [GFC2A](#)



Power Protection Products, GFCI Linecords, Commercial, Auto Set, 15A 125V AC, 5-15R, 2' Cord Length, 4-6 mA Trip Level, Yellow

General

Application	GFCI Line Cords
Catalog Number	GFC2A
Color	Black, Yellow
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Industrial/Commercial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Automatic Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Line Cord
UPC	781786615038

Dimensions

Outside Diameter	0.35
Weight	0.8 lb

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

Product Assets

- [Catalog Page - BRY C-9 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Power Disruption Solutions](#)
- [Literature - General Literature - GFCI Portable Plug](#)
- [Literature - General Literature - Healthcare Solutions](#)
- [Literature - General Literature - BRYANT® Wiring Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-GFC2A-SPEC-EN | REV 6/2024