



Power Protection Products, GFCI Linecords, Commercial, Auto Set, 15A 125V AC, 5-15R, 25' Cord Length, 4-6 mA Trip Level, Yellow

By Bryant
Catalog # [GFCI2515](#)



Power Protection Products, GFCI Linecords, Commercial, Auto Set, 15A 125V AC, 5-15R, 25' Cord Length, 4-6 mA Trip Level, Yellow

General

Application	GFCI Line Cords
Catalog Number	GFCI2515
Color	Black, Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial/Commercial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Line Cord
UPC	781786916104

Dimensions

Outside Diameter	0.35
Weight	3.4 lb

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

Logistics

Carton Quantity	5
-----------------	---

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-GFCI2515-SPEC-EN | REV 6/2024