



# Triple Tap Portable Inline GFCI, Manual Set, 15A, 120V AC, 2' - 12/3 SJWTW

By Bryant  
Catalog # [GFCIST15125TRIM](#)

Heavy Duty Triple Tap Portable In Line GFCI, Manual Set, 15A, 120V AC, 2' - 12/3 SJWTW



\*Representative Image

## Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

## Application

Outdoor/Indoor

## General

Catalog Number	GFCIST15125TRIM
Color	Black/Yellow
Environmental Conditions	NEMA 3R
Material	Polycarbonate
Number Of Poles	2
Series	GFCI
Style	Triple Tap Outlet
Temperature Rating	-30°F (-35°C) - 150°F (66°C)
Type	Portable GFCI

UPC 783585694191

## Electrical Ratings

Amperage Rating	15 A
Phase	Single
Voltage Rating	120 V
Wattage	1800 W

## Conductor Related

Number Of Wires 3

## Certifications And Compliance

Industry Standard(s)	cULus 943
Nema Rating	5-15

## Product Assets

- [Installation Manuals - PD2168](#)
- [Sales Drawings - M14729](#)
- [Specifications - GFCIST15125TRIM](#)
- [Warranty - Industrial & Commercial Products](#)