



# Power Protection Products, GFCI Linecords, Commercial, Auto Set, 15A 125V AC, 5-15R, 15' Cord Length, 4-6 mA Trip Level, Yellow

By Bryant  
Catalog # [GFCL15A](#)

Power Protection Products, GFCI Linecords, Commercial, Auto Set, 15A 125V AC, 5-15R, 15' Cord Length, 4-6 mA Trip Level, Yellow



## Application

GFCI Line Cords

## General

Color	Black
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Industrial/Commercial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Automatic Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Line Cord
UPC	781786615076

## Dimensions

Outside Diameter	0.35
Weight	1.6 lb

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

## Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number Of Conductors	3
Strands	Multi

## Certifications and Compliance

Nema Rating	5-15P
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant C-9 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Power Disruption Solutions](#)  
[Literature - General Literature - GFCI Portable Plug](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-GFCL15A-SPEC-EN | REV 7/2023