



Portable GFCI Plug, Automatic Set, 15A, 120V AC, 15' with flying leads - 14/3 SJEOW

By Bryant
Catalog # [GFCLST15A](#)

Circuit Guard® Heavy Duty OEM Equipment Integrated Cord Set with Automatic Set, 15A, 120V AC, 15' with flying leads - 14/3 SJEOW



*Representative Image

Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Application

Outdoor/Indoor

General

Catalog Number	GFCLST15A
Color	Black
Environmental Conditions	NEMA 3R
Material	Polycarbonate
Number Of Poles	2
Series	GFCI
Style	Wire Leads
Temperature Rating	-30°F (-35°C) - 150°F (66°C)
Type	Portable GFCI

UPC 781786965683

Electrical Ratings

Amperage Rating	15 A
Phase	Single
Voltage Rating	120 V
Wattage	1800 W

Conductor Related

Number Of Wires 3

Certifications And Compliance

Industry Standard(s)	cULus 943
Nema Rating	5-15

Product Assets

- [Installation Manuals - PD3068](#)
- [Sales Drawings - M14742](#)
- [Specifications - GFCLST15A](#)
- [Warranty - Industrial & Commercial Products](#)