



Power Protection Products, GFCI Plugs, Commercial, Auto Set, 15A 125V AC, 5-15R, Plug Only, 4-6 mA Trip Level, Black

By Bryant
Catalog # [GFP15A](#)

Power Protection Products, GFCI Plugs, Commercial, Auto Set,
15A 125V AC, 5-15R, Plug Only, 4-6 mA Trip Level, Black



Application

Wired On GFCI Protection

General

Color	Black
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Industrial/Commercial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Automatic Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Plugs
UPC	781786615014

Dimensions

Outside Diameter	0.35
Weight	0.35 lb

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In, Wired On
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number Of Conductors	3
Strands	Multi

Certifications and Compliance

Nema Rating	5-15P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant C-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Power Disruption Solutions](#)
[Literature - General Literature - GFCI Portable Plug](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFP15A-SPEC-EN | REV 7/2023