



Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 15A, Brown

By Bryant
Catalog # GFR15



Power Protection Devices, Receptacle, Self Test, GFCI, 15A 125V,
2-Pole 3-Wire Grounding, 5-15R, Brown

Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

General

| | |
|-------------------|---|
| Catalog Number | GFR15 |
| Color | Brown |
| EU RoHS Indicator | Contact Manufacturer |
| Series | Heavy Duty |
| Specifications | <ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass |
| Style | Standard |
| Type | Standard |

UPC 883778999017

Electrical Ratings

| | |
|----------------------------|-------|
| Current / Amperage Rating | 15 A |
| Voltage Rating Description | 125 V |

Certifications And Compliance

| | |
|----------------------|-----------------------------|
| Industry Standard(s) | Meets All NEC® Requirements |
| Nema Rating | 5-15R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Engineering Drawing - M-13585 AutoCAD Drawing](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFR15](#)
- [Specifications - WIRING_GFR15_spec](#)