



Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 20A, Gray

By Bryant
Catalog # [GFR20GRY](#)



Power Protection Devices, Receptacle, Self Test, GFCI, 20A 125V,
2-Pole 3-Wire Grounding, 5-20R, Gray

Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

General

| | |
|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | GFR20GRY |
| Color | Gray |
| EU RoHS Indicator | Contact Manufacturer |
| Series | Heavy Duty |
| Specifications | <ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass |
| Style | Standard |
| Type | Standard |

UPC 883778999093

Electrical Ratings

| | |
|----------------------------|-------|
| Current / Amperage Rating | 20 A |
| Voltage Rating Description | 125 V |

Certifications And Compliance

| | |
|----------------------|-----------------------------|
| Industry Standard(s) | Meets All NEC® Requirements |
| Nema Rating | 5-20R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Engineering Drawing - M-13585 AutoCAD Drawing](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFR20GRY](#)
- [Specifications - WIRING_GFR20GRY_spec](#)