



# Heavy Duty Commercial AUTOGUARD® Self-Test GFCI Receptacle, 20A, Light Almond

By Bryant  
Catalog # [GFR20LA](#)



Power Protection Devices, Receptacle, Self Test, GFCI, 20A 125V,  
2-Pole 3-Wire Grounding, 5-20R, Light Almond

## Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

## General

Catalog Number	GFR20LA
Color	Light Almond
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"> <li>• Base - Nylon</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> <li>• Mounting Screws - Zinc plated steel</li> <li>• Mounting Strap - Zinc plated steel</li> <li>• Power Contacts - Brass</li> </ul>
Style	Standard
Type	Standard

UPC 883778999116

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

## Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Engineering Drawing - M-13585 AutoCAD Drawing](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - WIRING\\_GFR20LA\\_spec](#)
- [Specifications - GFR20LA](#)