



# Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, US Product

By Bryant

Catalog # [GFRST15IU](#)



Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, US Product

## Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction

## General

Catalog Number	GFRST15IU
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Ground Contacts - Brass</li><li>• Mounting Screws - Zinc plated steel</li><li>• Mounting Strap - Zinc plated steel</li><li>• Power Contacts - Brass</li></ul>

Style	Assembled In USA
Type	Standard
UPC	883778124143

## Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

## Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK K-5 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - GFRST15IU](#)