




Power Protection Products, GFCI Receptacle, Self Test, Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, With Alarm, Red

By Bryant
Catalog # [GFRST20RB](#)

Power Protection Products, GFCI Receptacle, Self Test,
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
With Alarm, Red



Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction
- Alarm version provides audible notification of a trip condition

General

Color	<ul style="list-style-type: none">• Red• Rouge
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Alarm
Type	Standard
UPC	883778228148

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant C-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - CIRCUITPRO® Self Test GFCI](#)
[Literature - 2015 UL GFCI Requirements](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFRST20RB-SPEC-EN | REV 7/2023