



Straght Blade Devices, SNAP-Connect, AUTOGUARD, Self Test, GFCI Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black

By Bryant
Catalog # [GFRST20SNAPBK](#)

Straght Blade Devices, SNAP-Connect, AUTOGUARD, Self Test, GFCI Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black



Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

Application

Commercial Grade

General

Color	<ul style="list-style-type: none"> • Black • Noir
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Item Type	Style Line GFCI Receptacle
Material	Nylon
Series	Heavy Duty
Style	Standard
Type	<ul style="list-style-type: none"> • Standard • Standard
UPC	883778124518

Dimensions

Dimensions	3.28 in x 1.77 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.77 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Wire Size	#12 AWG
-----------	---------

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFRST20SNAPBK-SPEC-EN | REV 7/2023