



# Power Protection Products, GFCI Receptacle, Self Test, Commercial Grade, 20A 125V, 2-Pole 3-WireGrounding, 5-20R, With Alarm, White

By Bryant  
Catalog # [GFRST20WB](#)

Power Protection Products, GFCI Receptacle, Self Test, Commercial Grade, 20A 125V, 2-Pole 3-WireGrounding, 5-20R, With Alarm, White



## Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction
- Alarm version provides audible notification of a trip condition

## General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Alarm
Type	Standard
UPC	883778228155

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

## Certifications and Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK K-5 Catalog Page](#)  
[Catalogs - Wiring Device-Kellems Full Catalog](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - CIRCUITPRO® Self Test GFCI](#)  
[Literature - 2015 UL GFCI Requirements](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-GFRST20WB-SPEC-EN | REV 7/2023