



# Heavy Duty Commercial Tamper-Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Black

By Bryant  
Catalog # [GFRTR20BLK](#)



Power Protection Devices, Receptacle, Self Test, GFCI, TR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Black

## General

Catalog Number	GFRTR20BLK
Color	Black
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Ground Contacts - Brass</li><li>• Mounting Screws - Zinc plated steel</li><li>• Mounting Strap - Zinc plated steel</li><li>• Power Contacts - Brass</li></ul>
Style	Standard
Type	Tamper-Resistant
UPC	883778999635

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

## Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFRTR20BLK](#)
- [Specifications - WIRING\\_GFRTR20BLK\\_spec](#)