



Heavy Duty Commercial Tamper Resistant Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, White

By Bryant
Catalog # [GFRTW15W](#)



Power Protection Devices, Receptacle, Self Test, GFCI, TRWR, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

General

Catalog Number	GFRTW15W
Color	White
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant, Weather Resistant
UPC	883778999345

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFRTW15W](#)
- [Specifications - WIRING_GFRTW15W_spec](#)