



# Power Protection Devices, Receptacle, Self Test, GFCI, TRWR, Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Red

By Bryant  
Catalog # [GFRTW20R](#)



Power Protection Devices, Receptacle, Self Test, GFCI, TRWR,  
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,  
Red

## Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

## General

Catalog Number	GFRTW20R
Color	Red
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"> <li>• Base - Nylon</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> <li>• Mounting Screws - Zinc plated steel</li> <li>• Mounting Strap - Zinc plated steel</li> <li>• Power Contacts - Brass</li> </ul>
Style	Standard

Type	Tamper-Resistant, Weather Resistant
UPC	883778999406

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

## Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFRTW20R](#)
- [Specifications - WIRING\\_GFRTW20R\\_spec](#)