



Heavy Duty Commercial Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Black

By Bryant
Catalog # [GFRWR20BLK](#)



Power Protection Devices, Receptacle, Self Test, GFCI, WR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black

Features

- Patented AUTOGUARD® self test technology
- Meets NEC requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

General

| | |
|-------------------|--|
| Catalog Number | GFRWR20BLK |
| Color | Black |
| EU RoHS Indicator | Contact Manufacturer |
| Series | Heavy Duty |
| Specifications | <ul style="list-style-type: none"> • Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass |
| Style | Standard |
| Type | Weather Resistant |

UPC 883778999772

Electrical Ratings

| | |
|----------------------------|-------|
| Current / Amperage Rating | 20 A |
| Voltage Rating Description | 125 V |

Certifications And Compliance

| | |
|----------------------|-----------------------------|
| Industry Standard(s) | Meets All NEC® Requirements |
| Nema Rating | 5-20R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - GFRWR20BLK](#)
- [Specifications - WIRING_GFRWR20BLK_spec](#)