




# Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Resistant, Hospital Grade, 15A 125V, 5-15R, With Night Light

By Bryant  
Catalog # [GFST82ALNL](#)



Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Resistant, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Almond, With Night Light

## Features

- Self Test
- IG
- Tamper and Weather Resistant
- Hospital Grade
- 15A 125V

## General

Catalog Number	GFST82ALNL
Color	Almond
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Standard
Type	Heavy Duty
UPC	781786150904

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Literature - CIRCUITPRO® Self Test GFCI Specifications - GFST82ALNL](#)