



GFCI Receptacle, Self Test, IG, Tamper and Weather Resistant, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Almond, With Night Light

By Bryant
Catalog # [GFST82ALZ](#)

Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Resistant, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Almond, With Night Light



General

Color	Almond
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Standard
Type	Heavy Duty
UPC	781786150584

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets



A proud member of the Hubbell Family.