



# Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Restant, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant  
Catalog # [GFST82BKIG](#)



Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Restant, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black

## Features

- Self Test
- IG
- Tamper and Weather Restant
- Hospital Grade
- 15A 125V

## General

Catalog Number	GFST82BKIG
Color	Black
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant, Weather Resistant
Type	Heavy Duty
UPC	781786150430

## Electrical Ratings

Amperage Rating	15 A
-----------------	------

Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY B-8 Catalog Page](#)  
[Catalog Page - BRY C-5 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - CIRCUITPRO® Self Test GFCI](#)  
[Specifications - GFST82BKIG](#)