



15A COMM HG SELF TEST TR ALARM GFR GRAY

By Bryant
Catalog # [GFST82GYTRB](#)

15A COMM HG SELF TEST TR ALARM GFR GRAY



General

Color	Gray
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant
Type	Heavy Duty
UPC	781786390188

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Bryant C-3 Catalog page](#)
[Catalog Page - Bryant B-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - CIRCUITPRO® Self Test GFCI](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFST82GYTRB-SPEC-EN | REV 7/2023