



# Receptacle, 20A, Comm, HG, Seft test, Tamper Resistant, Alarm, GFR, Almond

By Bryant  
Catalog # [GFST83ALTRB](#)

Receptacle, 20A, Comm, HG, Seft test, Tamper Resistant, Alarm, GFR, Almond



## General

Color	Almond
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant
Type	Heavy Duty
UPC	781786390249

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications and Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

[Literature - CIRCUITPRO® Self Test GFCI](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-GFST83ALTRB-SPEC-EN | REV 7/2023