



Power Protection Products, GFCI Receptacles, Self Test, Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R, Black

By Bryant
Catalog # [GFST83BKTR](#)



Power Protection Products, GFCI Receptacles, Self Test, Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R, Black

Features

- Self Test
- Tamper and Weather Resistant
- Hospital Grade
- 20A 125V
- 2-Pole 3- Wire Grounding

General

Catalog Number	GFST83BKTR
Color	Black
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant, Weather Resistant
Type	Heavy Duty
UPC	781786150355

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A

Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY B-8 Catalog Page](#)
- [Catalog Page - BRY C-5 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI Specifications - GFST83BKTR](#)