



20A COMM HG SELF TEST TR ALARM GFR GRAY

By Bryant

Catalog # [GFST83GYTRB](#)

20A COMM HG SELF TEST TR ALARM GFR GRAY



General

Color	Gray
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant
Type	Heavy Duty
UPC	781786390263

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - BRY B-7 Catalog Page](#)
- [Catalog Page - BRY C-3 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)