



# Power Protection Products, GFCI Receptacles, Self Test, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Bryant  
Catalog # [GFST83I](#)



Power Protection Products, GFCI Receptacles, Self Test, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

## Features

- Self Test
- Hospital Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

## General

Catalog Number	GFST83I
Color	Ivory
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Standard
Type	Heavy Duty
UPC	781786150218

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A

Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY B-7](#)
- [Catalog Page - BRY C-4](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI Specifications - GFST83I](#)