



## 20A COMM HG SELF TEST TR ALARM GFR IVORY

By Bryant  
Catalog # GFST83ITRB

20A COMM HG SELF TEST TR ALARM GFR IVORY



### Features

Self Test

### General

Catalog Number	GFST83ITRB
Color	Ivory
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant
Type	Heavy Duty
UPC	781786390270

### Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Number Of Wires 3-Wire

### Certifications And Compliance

Nema Rating 5-20R

### Logistics

Carton Quantity 25

### Product Assets

[Catalog Page - BRY B-7 Catalog Page](#)  
[Catalog Page - BRY C-3 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - CIRCUITPRO® Self Test GFCI Specifications - GFST83ITRB](#)